## Permit for use of special seals

Published: 28.10.2022.

Price Execution deadline in working days
Free - Learn moreClose - Learn moreClose

Execution deadline in working days Pecipient Receiving restrictions
- Private law legal person - Learn moreClose

O Description:

Standard time – 100 days. Maximum allowable time - 120-150 days.

Description:

Persons established in the customs territory of the Union Regulation No 952 / 2013 5, within the meaning of Section 31. Person (applicant) must have registered with the European Commission in the central information system (EORI system).

Authorisation to use special seals to ensure the identification of goods placed under the Union transit procedure and to prevent uncontrolled access to goods subject to the transit procedure.

The authorisation shall be granted where the customs authorities declare the seals for vehicles, containers and packages indicated in the application for authorisation valid.

Process description Related documents

## Process description

## Service requests

Permission to use special seals shall be granted if applicants demonstrate the ability to comply with regulations. In order to obtain an authorisation, an application shall be made to the Customs Decision System (CDS - EU Trader Portal) using the SRS Electronic Declaration System (EDS) (<a href="https://eds.vid.gov.lv/login/">https://eds.vid.gov.lv/login/</a> - Connect to European Information Systems - Customs Decision System (CDS - EU Trader Portal) - Applications - New Application).

The customs authority has 30 days to check whether all conditions are fulfilled and will notify the applicant of the decision. The application date is registered when the customs authority has received all necessary information.

## Receipt of services

The decision regarding the authorisation for the use of seals of a special type (favourable or unfavourable) shall be communicated by electronic means to the economic operator (applicant) in the Customs decision system.

https://www.vid.gov.lv/en/services/permit-use-special-seals